




Airline

A U T O M A T I O N



Laboratory Isolation Enclosures

- ▶ Protect lab personnel from fumes or gases.
- ▶ Prevent contamination of lab environment.

Custom modular cleanrooms also available.



Custom Lab Tables



Let Airline design, build and install your enclosure or table!

www.airlinehyd.com
800-999-SERV (7378)

Custom Laboratory Isolation Enclosures from Airline




Choose from a wide range of door options.

OPTIONAL FEATURES:

- ▶ **HEPA Fan Filter Modules:** 24"x48", 115 VAC 60 Hz., 62db @ 90 FPM noise level, adjustable air velocity range of 50-120, filter is PSL challenged. Includes mounting brackets & hardware. Available in 24"x24".
- ▶ **Fluorescent Light Fixtures:** 115VAC 60 Hz., single unit is designed for mounting outside of enclosure. Standard fluorescent lamps shipped loose.
- ▶ **Germicidal Ultraviolet Irradiator Light Fixtures:** Single lamp fixtures. 48" long. Units will deliver 19.3 watts of ultraviolet output (rated at 254 nanometers at 100 hours and 80 deg. F) 120 VAC 60 Hz are standard. Includes mounts, hardware and brackets. Other lengths available.
- ▶ **Custom Controls** (application specific)



Walk-in hoods provide huge savings over dedicated rooms with special ventilation.



AIRLINE SERVICES:

- ▶ On-site consultation & sketch of basic design
- ▶ 3D CAD drawing with quotation
- ▶ Fabrication options include machined kitting or complete assembly
- ▶ Fast and easy installation, if required



Custom Laboratory Tables



Airline

Fluid Power, Automation and Motion Control for All Industries

Airline Hydraulics Corporation

HEADQUARTERS: 3557 Progress Dr., Bensalem, PA 19020
Phone: (215) 638-4700 • Fax: (215) 638-1707

Call toll free: 1-800-999-SERV

York, PA(717) 767-6466
Pittsburgh, PA(412) 963-6633
Rochester, NY(585) 458-6430
North Kingstown, RI(401) 583-0190
North Billerica, MA(978) 353-0200